



ESKA FUSES

FUSE SELECTION GUIDE

CAR FUSES

Mini	Product Range : 341.100 Type : Mini Current : 2 A - 30 A voltage : 32 V breaking capacity : 1000 A
Standard	Product Range : 340.000 Type : Standard Current : 1 A - 40 A voltage : 32 V breaking capacity : 1000 A
Maxi	Product Range : 343.000 Type : Maxi Current : 30 A - 100 A voltage : 32 V breaking capacity : 1000 A
Midi+Mega+Power	Product Range : 341.400 Type : Midi Current : 30 A - 125 A voltage : 32 V breaking capacity : 1000 A
Midi+Mega+Power	Product Range : 341.300 Type : Mega Current : 100 A - 250 A voltage : 32 V breaking capacity : 1000 A
Midi+Mega+Power	Product Range : 341.500 Type : CAL Current : CAL.1 - CAL.4 voltage : 32 V breaking capacity : 1000 A
ATS	Product Range : 300.000 Type : ATS Current : 5 A - 25 A voltage : 36V breaking capacity : -
Streifen	Product Range : 341.200 Type : Strip protection Current : 30 A - 100 A voltage : 32 V breaking capacity : 1000 A

ESKA: PRODUCT OVERVIEW

PART NUMBER DESCRIPTION

Select part number for more specific information

341.120	2 A/32V/1000 A
341.122	3 A/32V/1000 A
341.123	4 A/32V/1000 A
341.124	5 A/32V/1000 A
341.126	7,5 A/32V/1000 A
341.127	10 A/32V/1000 A
341.129	15 A/32V/1000 A
341.131	20 A/32V/1000 A
341.132	25 A/32V/1000 A
341.133	30 A/32V/1000 A
343.403	30 A/32V/1000 A
343.404	40 A/32V/1000 A
343.405	50 A/32V/1000 A
343.406	60 A/32V/1000 A
343.407	70 A/32V/1000 A
343.408	80 A/32V/1000 A
343.410	100 A/32V/1000 A
341.410	30 A/32V/1000 A
341.414	40 A/32V/1000 A
341.415	50 A/32V/1000 A
341.416	60 A/32V/1000 A
341.417	70 A/32V/1000 A
341.418	80 A/32V/1000 A
341.420	100 A/32V/1000 A
341.425	125 A/32V/1000 A
341.310	100 A/32V/1000 A
341.312	125 A/32V/1000 A
341.315	150 A/32V/1000 A
341.317	175 A/32V/1000 A
341.320	200 A/32V/1000 A
341.322	225 A/32V/1000 A
341.325	250 A/32V/1000 A
341.510	CAL. 1/32V/1000 A
341.520	CAL. 2/32V/1000 A
341.530	CAL. 3/32V/1000 A
341.540	CAL. 4/32V/1000 A
300.024	5 A/36V/100
300.026	8 A/36V/100
300.030	16 A/36V/100
300.032	25 A/36V/100
341.233	30 A/32V/100
341.235	40 A/32V/100
341.237	50 A/32V/100
341.239	60 A/32V/100
341.241	80 A/32V/100
341.243	100 A/32V/100

S 58	Product Range : Type : Current : voltage : breaking capacity :	01.01400 KFZ-Mini 30 A 32 V -
S 59	Product Range : Type : Current : voltage : breaking capacity :	01.00335 KFZ-Mini/Standard 30 A 32 V -
S 60	Product Range : Type : Current : voltage : breaking capacity :	03.1300 KFZ-Standard 21 A 32 V -
S 61	Product Range : Type : Current : voltage : breaking capacity :	03.00345 KFZ-Standard 21 A 32 V -
S 62	Product Range : Type : Current : voltage : breaking capacity :	03.00400 KFZ-Standard Please Call 32 V -
	Product Range : Type : Current : voltage : breaking capacity :	03.00341 KFZ-Standard 21 A 50 V -
	Product Range : Type : Current : voltage : breaking capacity :	01.00350 KFZ-Standard 14 A 32 V -
	Product Range : Type : Current : voltage : breaking capacity :	370.000 KFZ-Standard 20 A 32 V -
S 66	Product Range : Type : Current : voltage : breaking capacity :	03.00420 KFZ-Standard 15 A 32 V -
	Product Range : Type : Current : voltage : breaking capacity :	01.00334 KFZ-Standard Please Call Please Call -
	Product Range : Type : Current : voltage : breaking capacity :	380.000 KFZ-Standard 30 A 32 V -
	Product Range : Type : Current : voltage : breaking capacity :	350.000 KFZ-Standard 30 A 32 V -

	Product Range : 341.501 Type : Fuse Puller Current : - voltage : - breaking capacity : -
S 71	Product Range : 03.00360 Type : KFZ-Midi Current : 125 A voltage : Please Call breaking capacity : -
S 71-2	Product Range : 03.00370 Type : KFZ-Midi Current : 125 A voltage : 32 V breaking capacity : -
S 72	Product Range : 03.00380 Type : KFZ-Mega Current : 30 A - 100 A voltage : 32 V breaking capacity : -
S 73-1	Product Range : 03.00300 Type : KFZ-ATS Current : 30 A - 100 A voltage : Please Call breaking capacity : -
Z 73-2	Product Range : 03.00306 Type : KFZ Current : 30 A - 100 A voltage : Please Call breaking capacity : -
S 73-3	Product Range : 01.00303 Type : KFZ-ATS Current : 30 A - 100 A voltage : Please Call breaking capacity : -
S 73-4	Product Range : 01.00304 Type : KFZ-ATS Current : 30 A - 100 A voltage : Please Call breaking capacity : -

[Back to top](#)



[HOME](#) |
 [ABOUT US](#) |
 [FUSE SEARCH](#) |
 [QUOTE](#) |
 [SITEMAP](#)

CONTACT POWERFUSE TODAY

TOLL-FREE: (800) 739-914 | (918) 665-6888