TJ04315300J0G

TJ04315300J0G - Terminal Blocks : Pluggable plug, 3.81mm pitch, horizontal wire-inlet, 4 position

ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More
Contact our sales/technical support
Sample request



Customer drawing

Environmental Compliance Report

Specifications | Download document

Dimensional	General	Mechanical	Electrical	Physical	Approvals / Certifications

Dimensional	
Strip length (Wire)	6 to 7 mm
Solid wire size (AWG)	16 to 28
Solid wire size (mm2)	1.5
Stranded wire size (AWG)	16 to 28
Stranded wire size (mm2)	1.5
Pitch	3.81 mm
Screw Size	M2
General	
Gender	Female plug
Packaging	Box
Product Type	Screw Pluggable System
Series	TJ
Number of Positions	4
Mechanical	
Number of mating cycles	200
Electrical	
Withstanding Voltage	1.6 kV
Current rating	10 A
Voltage rating	300 V
Physical	
Color (Housing)	Green
Conductor entry angle	0°
Material (Housing)	Thermoplastic UL94V-0
Terminal material	Phosphor bronze
Terminal plating	Tin
Screw material	Steel
Screw plating	Zinc
Clamp material	Brass
Clamp plating	Nickel
Connection Type	Screw connection
Temperature (Operating - range)	-40 to 115 Celcius
Torque	3.0 Lb-in
Approvals / Certifications	
Approvals / Certifications	cULus, VDE

Downloaded from Arrow.com.