

# C4532CH2A104J320KA

TDK Item Description : C4532CH2A104JT\*\*\*



## Application & Main Feature

Commercial Grade ( Mid Voltage (100 to 630V) )

## Series

C4532 [EIA CC1812]



## Dimensions

L 4.50mm +/-0.4mm  
W 3.20mm +/-0.4mm  
T 3.20mm +/-0.3mm  
B 0.20mm Min.  
G

## Temperature Characteristic

CH (-25 to 85 degC 0+/-60ppm/degC)

## Rated Voltage

2A (100Vdc)

## Capacitance

100nF

## Capacitance Tolerance

J (+/-5%)

## O Factor

1000 Min.


## Insulation Resistance

5Gohm Min.


## AEC-Q200

Not Applicable


**|Z|, ESR vs. Freq. Characteristics**




**DC Bias Characteristic**



**Cap. vs. Freq. Characteristic**



**Temperature Characteristics**



All specifications are subject to change without notice.

January 4, 2016