





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	
A		UPDATE DIM.	3/14/18	AY/DH
B		UPDATE DIM.	7/15/21	LH/RL



Panel hole dimensions



SPECIFICATIONS:

Material:
 Insulator: Nylon66, rated UL 94V-2
 Insulator color: Natural
 Electrical:
 Voltage Rating: 600V Max.
 Current rating: 11 Amps Max.
 Insulation resistance: 1,000M ohms min
 Dielectric withstanding voltage: 5,000 VAC for 1 minute
 Temperature Rating:
 Operating temperature: -55°C to +105°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED			
INCHES		HOLES	
.X	±.10	Ø.X	±.10
.XX	±.020	Ø.XX	±.015
.XXX	±.015	Ø.XXX	±.010

DRAWN	TW	10/02/12
CHECKED	AY	10/02/12
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE: .250 [6.35MM] PITCH CONNECTOR, 9 POS
 HOUSINGS, MALE, VERTICAL

SIZE X	PART NO. DME-M-09-SQ	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1