

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

LOC	DIST
J	-


REVISIONS 変更


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED	18DEC2012	H.M	N.Y





スケール 2:1





RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

推奨基板取付穴寸法 : コネクタ搭載面(非累積公差)
PC基板厚 : 1.0~1.6±0.1

12	X	5	12.5	17.6	1-2040558-6
10	X	4	10.0	15.1	1-2040558-5
6	X	2	5.0	10.1	1-2040558-3
4	X	1	2.5	7.6	1-2040558-2
POS	KEY	n	A	B	PART NO

AS SHOWN : 20POS(X-KEY)

1. 材料:ハウジング:ガラス入り熱可塑性ポリエステル樹脂(94V-0)、色:黒
コンタクト:錫めっき済銅合金
リテンションレグ:錫めっき済銅合金
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

1. MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR:BLACK
CONTACT:PRE-TIN COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差 ±0.3,±5°
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-

MATERIAL 材料 1
FINISH 仕上 -

DWN	13MAY2008 M.MAEBASHI
CHK	13MAY2008 T.KUDO
APVD	13MAY2008 S.MANABE
PRODUCT SPEC 製品規格	108-78298
APPLICATION SPEC 取付適用規格	114-5377
WEIGHT	-

TE Connectivity

NAME 名称: DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATE 4-20POS

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C-2040558	-

CUSTOMER DRAWING | SCALE 尺度 4:1 | SHEET 1 OF 2 | REV C

1470-19 (3/11)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.


LOC	DIST
J	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1 OF 2			




1-2040558-2
4POS(X-KEY)




ONLY 4POS

推奨基板取付穴寸法 ： コネクタ搭載面（非累積公差）
PC基板厚 ： 1.0～1.6±0.1


RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0～1.6±0.1




1-2040558-3
6POS(X-KEY)





1-2040558-6
12POS(X-KEY)





1-2040558-5
10POS(X-KEY)























THIS DRAWING IS A CONTROLLED DOCUMENT.

SEE SHEET 1 OF 2

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL	FINISH -

DWN	M.MAEBASHI 13MAY2008
CHK	T.KUDO 13MAY2008
APVD	S.MANABE 13MAY2008
PRODUCT SPEC	108-78298
APPLICATION SPEC	114-5377
WEIGHT	-

TE Connectivity

NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATE 4-20POS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2040558	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 2 OF 2 | REV C

1470-19 (3/11)

Downloaded from Arrow.com.