

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0934446212  
**Status:** Active  
**Overview:** ML-XT Sealed Connection System  
**Description:** ML-XT Sealed 12 Circuit Receptacle Housing, Pre-Assembled with Large Rear Seal and Cover, Keying Option A, Grey



Series image - Reference only

|                                                         |                                                             |
|---------------------------------------------------------|-------------------------------------------------------------|
| <b>Documents:</b>                                       |                                                             |
| <a href="#">3D Model</a>                                | <a href="#">Application Specification 934430010-A (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                          | <a href="#">Packaging Specification 934430002-K (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>        |
| <a href="#">Product Specification 934430010-P (PDF)</a> | <a href="#">Product Literature (PDF)</a>                    |

**Agency Certification**  
UL E29179

|                             |                                |
|-----------------------------|--------------------------------|
| <b>General</b>              |                                |
| Product Family              | Crimp Housings                 |
| Series                      | 93444                          |
| Application                 | Power, Signal, Wire-to-Wire    |
| Overview                    | ML-XT Sealed Connection System |
| Product Literature Order No | 987651-0201                    |
| Product Name                | ML-XT                          |
| UPC                         | 889056307802                   |

|                               |                |
|-------------------------------|----------------|
| <b>Physical</b>               |                |
| Circuits (maximum)            | 12             |
| Color - Resin                 | Grey           |
| Gender                        | Receptacle     |
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | Yes            |
| Lock to Mating Part           | Yes            |
| Material - Resin              | Nylon          |
| Net Weight                    | 18.900/g       |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | N/A            |
| Polarized to Mating Part      | Yes            |
| Temperature Range - Operating | -55° to +125°C |

|                               |       |
|-------------------------------|-------|
| <b>Electrical</b>             |       |
| Current - Maximum per Contact | 13.0A |

**Material Info**

|                                    |               |
|------------------------------------|---------------|
| <b>Reference - Drawing Numbers</b> |               |
| Application Specification          | 934430010-A   |
| Packaging Specification            | 934430002-K   |
| Product Specification              | 934430010-P   |
| Sales Drawing                      | 934430060-000 |

**EU ELV**  
Not Relevant

|                                                                                                                                                                                                                                 |                                                                                               |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| <b>EU RoHS</b><br>Compliant<br><b>REACH SVHC</b><br>Not Contained Per -<br>ED/71/2019 (16 July<br>2019)<br><b>Halogen-Free</b><br><b>Status</b><br>Low-Halogen<br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b><br><br><br><br><br><br><br><br><br><br>China ROHS<br>ELV<br>RoHS Phthalates |
|                                                                                                                                                                                                                                 | Green Image<br>Not Relevant<br>Not Contained                                                  |

**Search Parts in this Series**  
93444 Series

**Mates With**  
ML-XT Sealed 12 Circuit Plug Housing  
934456212

**Use With**  
ML-XT Male (Pin) Terminal 845240004  
(Nickel), ML-XT Male (Pin) Terminal  
845240014 (Selective Gold), ML-XT 12  
Circuit Receptacle Wedgelock 93447 , ML-  
XT Blind Cavity Plug 934941000

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION