

3M

All 3M ProductsInnovationExplore 3M

SearchKeywords, part numbers, etc

United States [Change]

Electrical Commercial and Industrial

ProductsDocumentation & LiteratureNews & TradeshowSupport

United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications > Electrical Products > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Vinyl Electrical Tapes > Scotch® Vinyl Electrical Color Coding Tape 35-White-3/4, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

Find An Account RepWhere To Buy (Find A Distributor)Contact Us

Scotch® Vinyl Electrical Color Coding Tape 35-White-3/4, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

3M ID 80610833982UPC # 000540071082833M Product Number 35-WHITE-3/43M Product Number 35-White-3/4x66FT

PrintShare



Scotch® Vinyl Electrical Tape 35 is a polyvinyl chloride color-coding tape. Outstanding electrical and mechanical properties make this tape excellent for use in phase identification, and color coding of motor leads and piping systems.

Buy at Shop3M.com

Need Help?

Questions? We can help
[Contact Us](#)

Overview	Documentation																																
<div>Specifications</div> <table><tr><td>Adhesive Material</td><td>Rubber Resin</td></tr><tr><td>Agency Approvals</td><td>CSA, UL Listed</td></tr><tr><td>Backing Material</td><td>Polyvinyl Chloride</td></tr><tr><td>Breaking Strength</td><td>17 Ib/in</td></tr><tr><td>China RoHS - Below MCV</td><td>Yes</td></tr><tr><td>EU RoHS Compliant</td><td>Yes</td></tr><tr><td>Length</td><td>66 Linear Foot</td></tr><tr><td>Operating Temperature (Celsius)</td><td>0 to 105 Degree Celsius</td></tr><tr><td>Operating Temperature (Fahrenheit)</td><td>32 to 220 Degree Fahrenheit</td></tr><tr><td>Product Family</td><td>Scotch® Vinyl Color Coding Electrical Tape 35</td></tr><tr><td>Specifications</td><td>VDE 0340-TEIL1</td></tr><tr><td>Tape Grade</td><td>Premium</td></tr><tr><td>Tape Type</td><td>Vinyl</td></tr><tr><td>Thickness</td><td>7 Milli-inch (mil)</td></tr><tr><td>Voltage Application</td><td>Low Voltage</td></tr><tr><td>Width</td><td>3/4 Inch</td></tr></table>		Adhesive Material	Rubber Resin	Agency Approvals	CSA, UL Listed	Backing Material	Polyvinyl Chloride	Breaking Strength	17 Ib/in	China RoHS - Below MCV	Yes	EU RoHS Compliant	Yes	Length	66 Linear Foot	Operating Temperature (Celsius)	0 to 105 Degree Celsius	Operating Temperature (Fahrenheit)	32 to 220 Degree Fahrenheit	Product Family	Scotch® Vinyl Color Coding Electrical Tape 35	Specifications	VDE 0340-TEIL1	Tape Grade	Premium	Tape Type	Vinyl	Thickness	7 Milli-inch (mil)	Voltage Application	Low Voltage	Width	3/4 Inch
Adhesive Material	Rubber Resin																																
Agency Approvals	CSA, UL Listed																																
Backing Material	Polyvinyl Chloride																																
Breaking Strength	17 Ib/in																																
China RoHS - Below MCV	Yes																																
EU RoHS Compliant	Yes																																
Length	66 Linear Foot																																
Operating Temperature (Celsius)	0 to 105 Degree Celsius																																
Operating Temperature (Fahrenheit)	32 to 220 Degree Fahrenheit																																
Product Family	Scotch® Vinyl Color Coding Electrical Tape 35																																
Specifications	VDE 0340-TEIL1																																
Tape Grade	Premium																																
Tape Type	Vinyl																																
Thickness	7 Milli-inch (mil)																																
Voltage Application	Low Voltage																																
Width	3/4 Inch																																