**Part Number :** 192060005
**Product Description :** InsulKrimp Parallel Splice for 16-14 AWG Wire, Carton
**Series Number :** 19206
**Status :** Active
**Product Category :** Splices
**Engineering Part Number :** BS-V-304X



## Documents and Resources

### Drawings

192060005_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Splices |
| Series | 19206 |
| Description | InsulKrimp Parallel Splice for 16-14 AWG Wire, Carton |
| Product Name | InsulKrimp |
| Type | Parallel Splice |
| UPC | 800753052888 |

### Agency

| | |
|---|---|
| UL | E32244 |

### Physical

| | |
|---|---|
| Barrel Type | Closed |
| Color - Resin | Blue |
| Flammability | 94V-0 |
| Insulation | PVC |
| Material - Metal | Copper |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | PVC |
| Net Weight | 0.838/g |
| Packaging Type | Carton |

Downloaded from Arrow.com.

| | |
|---|---|
| Wire Insulation Diameter | 4.40mm max. |
| Wire Size (AWG) | 14, 16 |

## Application Tooling

## Global

| Description | Part Number |
|---|---|
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) | 640010100 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | 640160036 |



Downloaded from Arrow.com.