



HARNESSING

END CAPS



✓ Active

TE CONNECTIVITY (TE)

101A062-4-0

Raychem | CAP , CRPS

101A062-4-0

TE Internal Number: 843427-000

Alias ID: 7-1196579-4

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Product Type End Cap

Adhesive Type Adhesive Purchased Separately

Expanded Inside Diameter (Min) 25.4 mm [1 in]

Recovered Inside Diameter (Max) 11.4 mm [.45 in]

Material Modified Polyolefin



PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

Cap, Round End

PDF

English

Product Specifications

Product Specification

Thermofit Polyolefin Molded Components Flame-Retarded, Flexible, Heat-Shrinkable

PDF

English

Product Environmental Compliance

Safety Data Sheet

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type End Cap

Size Code 62

Body Features

Material Modified Polyolefin

Pliancy Flexible

Adhesive Pre-Coat No

Material Code 4

Dimensions

Expanded Inside Diameter (Min) 25.4 mm [1 in]
Recovered Inside Diameter (Max) 11.4 mm [.45 in]
Length 68 mm [2.7 in]
Recovered Wall Thickness (Nominal) 2.29 mm [.09 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 135
Resistance Protection Suitable for occasional exposure to fluids

Industry Standards

Government Qualified No

Other

Adhesive Type Adhesive Purchased Separately
Adhesive Code S1017, S1048

Statement of Compliance

Statement of Compliance

PDF