

Part Number : 1300130393
Product Description : Mini-Change A-Size Receptacle, 4 Poles, PG 13.5 Threads, Female (Straight) to 18 AWG Leads, 2.0m (6.56') Length
Series Number : 130013
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 1R4D04A16M020

Documents and Resources

Drawings

1300130393_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130013
Description	Mini-Change A-Size Receptacle, 4 Poles, PG 13.5 Threads, Female (Straight) to 18 AWG Leads, 2.0m (6.56') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678846007

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	2.0m
Material - Component	PVC
Mounting Thread Size	PG13.5
Net Weight	1.000/g
Orientation	Straight
Panel Mount	Front
Poles	4

Downloaded from Arrow.com.

Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1061
Wire Size (AWG)	18

Downloaded from Arrow.com.