




DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/05	
A		REDRAWN	9/19/11	



SPECIFICATIONS:

Material:

Insulator: Nylon 66, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Soldering: Brass, Tin Plated

Plating

Tin over Copper underplate overall

Electrical

Operating voltage: 250 VAC

Current rating: UL: 15 Amps max

VDE: 10 Amps max

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to $+70^{\circ}\text{C}$

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 235°C for 5 seconds

TERMINAL OPTIONS		
-1	-2	-3
.187 Q.C.	.250 Q.C.	.157 Solder
		

RECOMMENDED PANEL
CUT-OUT

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

IFC MAIL INLET / OUTLET

SNAP-IN PANEL MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010			
APPROVALS		DATE	
DRAWN	SS	6/17/05	
CHECKED			
APPROVED			
ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
TITLE			
IEC MALE INLET / OUTLET SNAP-IN PANEL MOUNT			
SIZE	PART NO.		
X	IEC-HS-X		
REF:	S00037T	SCALE:	NTS
SHEET 1 OF 1		REV. A	