THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST
J	

REVISIONS 変更

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	0	RELEASED	FJ00-1835-98	19/NOV/98	M.H	I.H
	A	REVISED	FJ00-0740-99	6/MAY/99	M.H	S.H


-2:AS SHOWN

NOTE

1 MATERIAL:GLASS FIELD THERMO PLASTIC,POLYESTER
COLOR:BLACK

注記

1 材料： ガラス入り熱可塑性ポリエステル樹脂
色：黒色



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位： 粍 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
一般公差
10≧ : ±0.2
30≧ >10 : ±0.25
100≧ >30 : ±0.3
ANGLE : ±3°

MATERIAL 材料: 注記参照 SEE NOTE

FINISH 仕上: 注記参照 SEE NOTE

DWN M.HIGO 30/SEP/98
CHK N.MATSUBARA 19/NOV/98
APVD I.HASEGAWA 19/NOV/98
PRODUCT SPEC 製品規格
APPLICATION SPEC 取付適用規格 114-5148
WEIGHT

WIRE RANGE 把合電線断面積 | INSULATION DIA 被覆外径

AMP 日本エー・エム・ピー株式会社 Kawasaki,Japan

NAME 名称: DYNAMIC D3500 DUMMY HSG

SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	00779	C- 1318182	

SCALE 尺度 4-1 SHEET 1 OF 1 REV A

Downloaded from Arrow.com.