



Pushing Performance
Since 1945

Han 24B top/side entry Hood HC M40



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 0598
Specification	Han 24B top/side entry Hood HC M40
HARTING eCatalogue	https://harting.com/19300240598

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® B
Type of hood/housing	Hood
Description of hood/housing	Special type
Type	High construction

Version

Size	24 B
Version	Top/side entry
Number of cable entries	2
Cable entry	1x M40 1x M40
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP66 IP67



Pushing Performance
Since 1945

Technical characteristics

Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

Specifications and approvals

Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	300 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140127029
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466