







SOCKETS

SOCKETS		
Product	Features	Accessory For
OT08PC Octal Socket 8-Pin 	8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals.	AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility
NDS-8 Octal Socket 8-Pin Screw terminals with captive wire clamps 	8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips.	Up to two #14 AWG (2.45 mm²) wire size Series: <div> <div>ARP</div> <div>FS500</div> <div>LLC4</div> <div>LLC5</div> </div> <div> <div>PRLM</div> <div>TDB</div> <div>TDBH</div> <div>TDBL</div> </div> <div> <div>TDI</div> <div>TDIH</div> <div>TDIL</div> <div>TDM</div> </div> <div> <div>TDMB</div> <div>TDMH</div> <div>TDML</div> <div>TDR</div> </div> <div> <div>TDS</div> <div>TDSH</div> <div>TDSL</div> <div>TRDU</div> </div> <div> <div>TRM</div> <div>TRS</div> <div>TRU</div> </div>
P1011-6 Octal Socket 8-Pin 	8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCRB8 hold-down brackets.	Series: <div> <div>ARP</div> <div>FS500</div> <div>LLC4</div> <div>LLC5</div> </div> <div> <div>PRLM</div> <div>TDB</div> <div>TDM</div> <div>TDMB</div> </div> <div> <div>TDR</div> <div>TDS</div> <div>TRB</div> <div>TRDU</div> </div> <div> <div>TRM</div> <div>TRS</div> <div>TRU</div> </div>
OT11PC Magna Socket 11-Pin 	Magna Sockets are for plug-in units	11-pin Plug-in units Series: <div> <div>ARP</div> <div>LLC6</div> <div>TDB</div> <div>TDBH</div> </div> <div> <div>TDBL</div> <div>TDMB</div> <div>TDS</div> <div>TDSH</div> </div> <div> <div>TDSL</div> <div>TRB</div> <div>TRDU</div> <div>TRM</div> </div> <div> <div>TRS</div> <div>TRU</div> </div>
SD12-PC Rectangle Socket 12-pin 	12-pin surface Rectangle Socket.	ACBC-120
NDS-11 11-pin Magna Socket Screw terminals with captive wire clamps 	11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips.	AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes Series: <div> <div>ARP</div> <div>LLC6</div> <div>TDB</div> <div>TDBH</div> </div> <div> <div>TDBL</div> <div>TDMB</div> <div>TDS</div> <div>TDSH</div> </div> <div> <div>TDSL</div> <div>TRB</div> <div>TRDU</div> <div>TRM</div> </div> <div> <div>TRS</div> <div>TRU</div> </div>