



Part Number : [1062920805](#)
Product Description : MMC Male-to-(2) MPO
Female Fiber Optic Breakout Patch Cord,
Singlemode, 16 Fiber BIF Plenum Cable, 5.0m
Length, Yellow Cable
Series Number : 106292
Status : Active
Product Category : Fiber Optic Cable
Assemblies



Documents & Resources

Drawings
[1062920805_sd.pdf](#)

Specifications
[1062920301-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106292
Description	MMC Male-to-(2) MPO Female Fiber Optic Breakout Patch Cord, Singlemode, 16 Fiber BIF Plenum Cable, 5.0m Length, Yellow Cable
Connector to Connector	MMC-to-(2) MPO
Mode	Singlemode
Product Name	MMC,MPO
UPC	198282432838

Physical

Boot Type	Straight
Cable Length	5.0m
Cable Size	2.50mm, 3.00mm
Fiber (Core/Cladding)	9/125µm
Net Weight	1.000/g
Single Ended	No
Wire/Cable Type	16 Fiber Bend-insensitive Plenum

This document was generated on Apr 22, 2025
