

4-Outlet Power Strip, 10 ft. (3.05 m) Cord, NEMA 5-15P Plug, 12 in.

MODEL NUMBER: **PS120410**



Metal 12 in. power strip distributes power to multiple devices in an industrial, office, retail, rackmount, raceway, workbench or point-of-sale setting.

Features

Ideal Power Distribution

- Recommended for industrial, office, retail, rackmount, raceway, workbench and point-of-sale settings
- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 10-ft. (3.05 m) power cord with NEMA 5-15P plug
- Meets UL1363 (USA) and cUL (Canada) certifications

Premium Safety Features

- 15A resettable circuit breaker prevents dangerous overloads
- Transparent switch cover eliminates accidental shutdowns
- Lighted on/off switch confirms operation at a glance

Rugged All-Metal Housing

- 12 in. length
- Hardware included for mounting on a wall, floor, workbench or under a counter

Highlights

- 4 NEMA 5-15R outlets with 1.77 in. center-to-center spacing
- 15A resettable circuit breaker
- Lighted on/off switch with transparent safety cover
- Heavy-duty all-metal housing
- 10-ft. (3.05 m) power cord with NEMA 5-15P plug

Package Includes

- PS120410 4-Outlet Power Strip, 10-ft. (3.05 m) Cord, 12 in.
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332198525
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

TRIPP LITE
SERIES

Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
Outlet Spacing	1.77in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	1.77 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.80 x 15.40
Shipping Dimensions (hwd / cm)	6.10 x 12.19 x 39.12
Shipping Weight (lbs.)	2.10
Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 12.000
Unit Dimensions (hwd / cm)	3.18 x 4.12 x 30.48



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	1.28
Unit Weight (kg)	0.58
Outlet Spacing	1.77 in.
Mounting Details	Includes mounting clips
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.