

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100043](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway™ 500W Twin Halogen Floodlight Stanchion Mount with Switch, Cord Type 12/3 SOOW, Cord Length 0.457m (1.50')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130110](#)
NEMA Configuration NEMA 5-20
NEMA Rating Rain Tight
Outlet Side
Overview [Wide-Area Lighting Products](#)
Product Literature Order No 987650-8054
Product Name Super-Safeway™
Type Wide Area Lamps
UPC 78678801180
Woodhead Yes

Physical

Cord Length - Primary 0.457m (1.50')
Cord Length - Secondary N/A
Depth 1.16m (3.80')
Duty Industrial
Guard Included No
Guard Type N/A
Height 2.29m (7.50')
Length 1.16m (3.80')
Material - Globe Tempered Glass
Material - Guard #10 Gauge Zinc-plated Steel
Mounting Style Stanchion
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
Cord Type - Primary 16/3 SOOW
Lamp Type T-3 RSC
Lamp Wattage - Maximum 500W
Lumens 9200
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number SBS2500



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed
ELV Not Reviewed

Search Parts in this Series

[130110](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION