

12TW1-10P

[Products](#) > [Switches](#) > [Toggle Switches](#) > [TW Series](#) > [12TW1-10P](#)

Overview

MICRO SWITCH TW Series Toggle Switch, 2 pole, 3 position, Solder terminal, Locking Lever, Military Part Number MS27754-38P....
[View More](#)



Technical Specifications

Series Name	TW
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vac to 115 Vac0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc
Action	3 position
Mounting	Bushing 15/32 in
MIL Spec. Number	MS27754-38P

Product Type	MICRO SWITCH Toggle Switch
Circuitry	DPDT
Circuitry/Operating action	
Termination	Solder
Lever Type	Locking

view all 12TW1-10P literature

view distributor inventory

sample request

email support

get support

email sales

find a distributor

email this page

[View More](#)

View documents in:

English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
12TW1-10P highres photo	Photo	English	2MB
12TW1-10P lowres photo	Photo	English	59KB
MICRO SWITCH TW Series Miniature Military-Grade Toggle Switches	Datasheet	English	1MB
Sensors and Switches in Oil Rig Applications	Application Note	English	7MB

[View More](#)

Product Features

- Qualified to MIL-DTL-83731
- Save space and weight
- SPDT and DPDT circuitry
- Temperature range: -65 °C to 71 °C [-85 °F to 160 °F]
- Sealed bushing versions
- Choice of 1/4 in or 15/32 in bushing
- Color tab available on 15/32 in. bushing
- UL recognized

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.