

SOCKETS

SOCKETS			
Product	Features	Accessory For	
OT08PC Octal Socket 8-Pin	 8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals.	AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility	
NDS-8 Octal Socket 8-Pin Screw terminals with captive wire clamps	 8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips.	Up to two #14 AWG (2.45 mm²) wire size Series: ARP FS500 LLC4 LLC5 PRLM TDB TDBH TDBL TDI TDIH TDIL TDM TDMB TDMH TDML TDR TDS TDSH TDSL TRDU TRM TRS TRU	
P1011-6 Octal Socket 8-Pin	 8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCR8 hold-down brackets.	Series: ARP FS500 LLC4 LLC5 PRLM TDB TDM TDBM TDR TDS TRB TRDU TRM TRS TRU	
OT11PC Maginal Socket 11-Pin	 Maginal Sockets are for plug-in units	11-pin Plug-in units Series: ARP LLC6 TDB TDBH TDBL TDML TDS TDSH TDSL TRB TRDU TRM TRS TRU	
SD12-PC Rectangle Socket 12-pin	 12-pin surface Rectangle Socket.	ACBC-120	
NDS-11 11-pin Maginal Socket Screw terminals with captive wire clamps	 11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips.	AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes Series: ARP LLC6 TDB TDBH TDBL TDML TDS TDSH TDSL TRB TRDU TRM TRS TRU	