

Heyco Products, Inc. "The First Name in Wire Protection"

HEYCO

**ALL NEW
PRODUCTS!**

Heyco® Liquid Tight Cordgrips Multi-Hole, PG Hubs



PART NO. Black	DESCRIPTIONS	GLAND CONFIGURATIONS	PART NO. Black	DESCRIPTIONS	GLAND CONFIGURATIONS
M3207GBA	LTCG 7	2- 1,5 mm holes	M3219GAJ	LTCG 16	2- 6,0 mm holes
M3210GH	LTCG 9	2- 1,7 mm holes	M3219GQ	LTCG 16	3- 3,0 mm holes
M3210GP	LTCG 9	2- 3,0 mm holes	M3219GX	LTCG 16	3- 4,0 mm holes
M3210GJ	LTCG 9	3- 1,7 mm holes	M3219GAH	LTCG 16	3- 5,6 mm holes
M3210GAP	LTCG 9	4- 1,4 mm holes	M3219GR	LTCG 16	4- 3,0 mm holes
M3210GK	LTCG 9	4- 1,7 mm holes	M3219GY	LTCG 16	4- 4,0 mm holes
M3210GM	LTCG 9	4- 2,3 mm holes	M3219GZ	LTCG 16	5- 4,0 mm holes
M3210GG	LTCG 9	5- 1,6 mm holes	M3219GS	LTCG 16	6- 3,0 mm holes
M3210GAZ	LTCG 9	6- 1,4 mm holes	M3219GW	LTCG 16	6- 3,8 mm holes
M3210GE	LTCG 9	10- 1,4 mm holes	M3219GBB	LTCG 16	6- 4,0 mm holes
M3213GP	LTCG 11	2- 3,0 mm holes	M3222GAN	LTCG 21	2- 7,4 mm holes
M3213GAK	LTCG 11	2- 4,0 mm holes	M3222GAQ	LTCG 21	2- 8,0 mm holes
M3213GF	LTCG 11	3- 1,5 mm holes	M3222GAF	LTCG 21	3- 5,2 mm holes
M3213GQ	LTCG 11	3- 3,0 mm holes	M3222GAM	LTCG 21	3- 7,0 mm holes
M3213GAY	LTCG 11	4- 2,8 mm holes	M3222GAD	LTCG 21	4- 5,0 mm holes
M3216GN	LTCG 13	2- 2,5 mm holes	M3222GAG	LTCG 21	4- 5,2 mm holes
M3216GT	LTCG 13	2- 3,8 mm holes	M3222GBC	LTCG 21	4- 6,0 mm holes
M3216GAB	LTCG 13	2- 4,2 mm holes	M3225GAS	LTCG 29	4- 9,0 mm holes
M3216GAC	LTCG 13	2- 5,0 mm holes	M3225GAX	LTCG 29	4- 9,5 mm holes
M3216GAE	LTCG 13	2- 5,2 mm holes	M3225GAL	LTCG 29	6- 6,5 mm holes
M3216GL	LTCG 13	3- 2,0 mm holes	M3204GAT	LTCG 36	5- 9,0 mm holes
M3216GQ	LTCG 13	3- 3,0 mm holes	M3204GAL	LTCG 36	6- 6,5 mm holes
M3216GX	LTCG 13	3- 4,0 mm holes	M3204GAR	LTCG 36	6- 8,0 mm holes
M3216GS	LTCG 13	6- 3,0 mm holes	M3204GAW	LTCG 36	7- 9,0 mm holes

Standard color black.

- All accompanying Cordgrips are made of nylon construction with TPE sealing glands that resist salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. This feature is not assessed by UL.
- **Locknuts INCLUDED.**
- For body part dimensions see page 2-12.
- Multi-hole glands are only to be used with Heyco Liquid Tight Cordgrips and are not sold separately.
- Consult Heyco for cordgrips molded in other colors.



Material	6/6 Nylon with TPE sealing gland
Flammability Rating	94V-2 Standard
Temperature Rating	-22°F (-30°C) to 212°F (100°C)
IP Rating	IP 68

*Quick
Specs*