Part Number : 1301470111
Product Description : Watertite Extreme Connector with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V, Cord Grip Body Size F4
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 29W77



Documents and Resources

Drawings

1301470111_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Connector with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V, Cord Grip Body Size F4
IP Rating	IP69K
NEMA Configuration	NEMA L17-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678871336

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 600V

Physical

Cord Grip Body Size	F4 1"

Downloaded from Arrow.com.

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	478.418/g
Poles	3-pole/4-wire
Receptacle Type	Single

Downloaded from Arrow.com.