



Part Number : [192030384](#)
Product Description : Krimptite Temp-Term
Butt Splice for 22-18 AWG Wire, 483°C (900°
F), Loose Piece
Series Number : 19203
Status : Active
Product Category : Splices



Documents & Resources


Drawings
[192030384_sd.pdf](#)

3D Models and Design Files
[192030384_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19203
Description	Krimptite Temp-Term Butt Splice for 22-18 AWG Wire, 483°C (900° F), Loose Piece
Product Name	Butt - Step Down,Krimptite,Temp-Terms
UPC	822348424733

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	0.761/g
Packaging Type	Carton
Temperature Range - Operating	483°C
Wire Insulation Diameter	3.60mm
Wire Size (AWG)	18, 20, 22

This document was generated on Mar 09, 2025