




Part Number : [508029101](#)
Product Description : 2.50mm Pitch Mini-Latch Crimp Terminal, Female, Brass, Bag
Series Number : 50802
Status : New Business Not Supported
Product Category : Crimp Terminals
Packaging Alternative : [0508029001 \(Reel\)](#)



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Crimp Terminals
Series	50802
Description	2.50mm Pitch Mini-Latch Crimp Terminal, Female, Brass, Bag
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Family	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
Product Name	Mini-Latch
UPC	800753370616

Electrical

Current - Maximum per Contact	3.0A
-------------------------------	------

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	56.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.15-1.90mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
-------------	-------------

Extraction and Activation Tool	<u>0638132700</u>
Hand Crimp Tool for 2.50mm Pitch SPOX Crimp Terminal, 22-28 AWG	<u>0638281900</u>

Application Tooling

Japan

Description	Part Number
Hand Crimp Tool JHTR5907	<u>0011260095</u>

This document was generated on Oct 30, 2023