Toggle S Series S-331F-J



*The photo is a sample image.
The color and shape may differ from the actual product.
*Please be sure to check the actual color and shape with a product sample.

PDF

Product Introduction

Plug-in type compact toggle switch (S series) - Tab terminal type: 2-pole single throw - Operating temperature range: -10 to 70° C - EU-RoHS compliant - Model number: S-331F-J

Product overview

Model Name	S-331F-J
category	toggle
series	S
Subcategory	Non-illuminated switch
Current capacity for detailed display1	20A 125V AC
Current capacity for detailed display 2	20A 250V AC
Current capacity 3 for detailed display	20A 30V DC
Operating temperature range (° C)	-10/+70
Number of poles	2 poles
Function 1	ON-OFF
Operation part shape	Basic lever
Terminal shape	tab
Panel mounting method	Screw mounting
Approximate dimensions of panel mounting holes (unit: mm)	12.5 Dia.
Approximate panel thickness for installation (unit: mm)	5.7 Max.
Obtained standards	UL
Acquired standard model name	S-331FUL-J
Environmental performance	RoHS

Specification changes

No.	category	overview	Publication date	PDF
418	Specification changes	Changes to the case material and other materials	March 13, 2025	
418	Specification changes	Changes to the case material and other materials	December 19, 2024	
352	Specification changes	Compliance with the EU RoHS Directive's prohibited substances standard for 10 substances was implemented for all shipments up to July 22, 2019.	April 26, 2019	
345	Orders and sales discontinued	Order acceptance for the successor product begins December 21, 2018.	December 11, 2018	

Back to Series TOP

NKKスイッチズ株式会社

© NKK SWITCHES CO., LTD.

Downloaded from Arrow.com.