

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039012240

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit Jr.™ Receptacle Housing, Dual Row, 24 Circuits, UL 94V-2, Natural

Documents:

3D Model

Drawing (PDF)

Product Specification PS-45750-001-001 (PDF)

Product Specification PS-5556-001 (PDF)

Product Specification TS-5556-002-001 (PDF)

Packaging Specification PK-5557-002-000 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5557
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. Glow Wire Equivalent Part.
MolexKits	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit Jr.™
UPC	800753584051
Physical	
Breakaway	No
Circuits (maximum)	24
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	4701.100/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	13.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	5557-24R
Reference - Drawing Numbers	
Packaging Specification	PK-5557-002-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the Contact Us section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

5557 Series

Mates With

5559 Dual Row, 5566 Vertical with Pegs,

5566 Vertical without Pegs, 5569 Right

Angle Dual Row with Flanges, 5569 Right

Angle Dual Row with Pegs, 43810 , 44068 ,

44281 , 87427 , 42404 , 42440

Use With

5556 Mini-Fit® Female Crimp Terminals,

45750 Mini-Fit® Plus HCS Crimp Terminal

This document was generated on 04/27/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION