



**Part Number :** 1301370130

**Product Description :** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

**Series Number :** 130137

**Status :** Active

**Product Category :** Power Distribution

**Engineering Number :** 3005-1B143



---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
--------	--------

Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids, 15.24m (50.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-15
Product Family	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678879664

### Agency

CSA	LR6837
UL	E38085

### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

### Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F2 1/2"
Cord Length	15.24m (50.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

---

This document was generated on Oct 02, 2024