

A



Clockwise view from mounting side

铭牌 Label Detail

铭牌 Label Detail

TYPE MS17HD4L4110-01
24VDC Max. 1A 0.305Nm
XXXXXXXXXX YY/MM/DD

Work Order 加工单号

MOONS'

Hybrid Stepping Motor

Shanghai Moons' Electric Co., Ltd.

This document is released for information only. Its reproduction in whole or in part or its dissemination to third parties is prohibited. All trademarks and registered trademarks appearing on this document are the property of their respective owners.

Type: MS17HD4L4110-01 Rev.B SCALE 1:1 Sheet 1 of 1

1	2	3	4	5	6	7	8
---	---	---	---	---	---	---	---

Unit: mm
第一角法

Unit: mm 每一齒面

未注线性与角度尺寸公差
Tolerances for linear and angular dimensions without individual tolerance indications

GB/T 1804-m eqv ISO 2768-1□m

未注形状与位置尺寸公差

Geometrical tolerance for features without individual tolerance indications

GB/T 1184-K eqv ISO 2768-2□K

UNLESS OTHERWISE SPEC

4

批准 API

三、准化: Standard

Technology

稽核 Check

1000

Design

NAMES

5

111

1001

1

1001

--	--

1001

7

1001

1001

3