

Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series

>

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



BB-02AFFM-QL8E01

Operating Temperature: -20°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: UL2238, UL50e

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

X-Lok, Standard...

AB-BB02ML-BBB...

-20°C ~ +80°C

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 10A	Connector Type Overmolded
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style N/A	
<div><div></div> More Options</div>	

People Also Bought

