


PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft. (1.22 m), Yellow

MODEL NUMBER: P004-004-YW



Yellow computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 4 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 4-ft. (1.22 m). The 4-ft. (1.22 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer power extension cord features a yellow SJT jacket and fully molded yellow ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332168351
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	

Highlights

- Recommended for powering computers, printers and other essential peripherals
- 4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded yellow for fast, easy identification in a crowded rack or workstation

Applications

- Connect devices like computers, servers and monitors to a PDU up to 4-ft. (1.22 m) away in your data center
- Extend an existing power connection up to 4-ft. (1.22 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-004 C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Yellow



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Plug Color	Yellow
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	4
Cable Length (m)	1.22
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Weight (kg)	0.19
Shipping Weight (lbs.)	0.42
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Storage Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/cUL, RoHS, REACH
Approvals	UL/CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>