



Item	Description	Unit
Screen Size (Diagonal)	1.5	inch
Controller IC	ST7712	--
Module Size	33.35 x 60.4 x 2.5	W x H x D (mm)
Active Area	26.112 x 28.16	W x H (mm)
LCD Type	Transmissive, a-Si TFT	--
Dot Number	128 x RGB x 128	W x H (dots)
Pixel Size	68 x RGB x 220	W x H (μm)
Pixel Arrangement	RGB Stripe	--
Viewing Direction	12	o'clock
Viewing Angle (R/L/U/D)	(40/40/35/15)	degree
Contrast Ratio	200:1	--
Color Saturation (NTSC)	60%	--
Response Time (Tr+Tf)	40ms (TYP)	ms

<i>PIN NO</i>	<i>1</i>	<i>2</i>	<i>3</i>	<i>4</i>	<i>5</i>	<i>6</i>	<i>7</i>	<i>8</i>	<i>9</i>	<i>10</i>
SYMBOL	VSS	VDD	/CS	RS	/WR	/RD	DB0	DB1	DB2	DB3
<i>PIN NO</i>	<i>11</i>	<i>12</i>	<i>13</i>	<i>14</i>	<i>15</i>	<i>16</i>	<i>17</i>	<i>18</i>	<i>19</i>	<i>20</i>
SYMBOL	DB4	DB5	DB6	DB7	DB8	DB9	DB10	DB11	DB12	DB13
<i>PIN NO</i>	<i>21</i>	<i>22</i>	<i>23</i>	<i>24</i>	<i>25</i>	<i>26</i>	<i>27</i>			
SYMBOL	DB14	DB15	/RESET	GND	VDD	LED(+)	LED(-)			