

M6/8.STP1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	M6/8.STP1
Product ID:	1SNA115529R1500
EAN:	3472591155297
Catalog Description:	M6/8.STP1 Screw Clamp Terminal Blocks - Disconnect with push-turn knob - with test socket - Grey, Orange
Long Description:	- Ease your disconnect operations with the disconnect 1/4 turn push-turn knob, - Possibility to seal in the open and closed position, - Ease your test operations with the built-in test socket.

Ordering

Color:	Grey, Orange
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	8 mm
Product Net Height:	55.5 mm
Product Net Depth / Length:	49 mm
Product Net Weight:	21 g

Technical

Rated Cross-Section:	6 mm ²
Spacing:	8 mm
Connection Type:	Screw clamp
Function:	Disconnect
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 6 mm ² Screw Clamp / Rigid 1x 0.5 ... 10 mm ²
Rated Current (I_n):	Main Circuit 15 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 720 A
Rated Voltage (U_r):	500 V

Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	11.0 mm
Recommended Screw Driver:	4 mm
Tightening Torque:	acc. IEC 60947-1 0.8 N·m Manufacturer 1 N·m

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 8 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161063A0200
Declaration of Conformity - CE:	1SND225015U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220002E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	62 mm
Package Level 1 Depth / Length:	230 mm
Package Level 1 Height:	64 mm
Package Level 1 Gross Weight:	0.525 kg

Package Level 1 EAN:	3472591155297
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 2 Gross Weight:	8.830 kg
Package Level 3 Units:	19200 piece
Product Packing Type:	Box

