



+ RELAYS, CONTACTORS & SWITCHES

DC



✓ Active

TE CONNECTIVITY (TE)

LEV100A6ANG=RELAY,SPST-NO,48VDC VMT 15

Kilovac | LEV100

3-1618391-7

TE Internal Number: 3-1618391-7

Alias ID: LEV100A6ANG

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Contact Arrangement 1 Form X, SPST-NO DM

Contact Current Rating (A) 100

Coil Voltage (Max) (VDC) 52

Coil Resistance (Ω) 392

Coil Voltage Rating (VDC) 48

[↓ 3D PDF](#)

DOCUMENTATION

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

5-1773450-5_sec7_LEV100

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Terminal Configuration 2 x M4 Bolt

Contact Type Sealed

Product Category Electromechanical Relays

Product Type Contactor

Product Classification Relays - Contactors

Configuration Features

Auxiliary Switch Contact Arrangement None

Electrical Characteristics

Coil Voltage (Max) (VDC) 52

Coil Resistance (Ω) 392

Coil Voltage Rating (VDC) 48

Contact Switching Voltage (Max) (VDC) 900

Actuating System DC

Contact Features

Contact Arrangement 1 Form X, SPST-NO DM

Contact Current Rating (A) 100

Number of Poles 1

Termination Features

Coil Termination Wire

Mechanical Attachment

Mounting Type Bottom

Dimensions

Coil Wire Length 381 mm [15 in]

Packaging Features

Packaging Method Individual

Other

Torque (in-lbs) 30 – 40

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
