




**Part Number :** [395265004](#)  
**Product Description :** 5.00mm Pitch Eurostyle  
Right-Angle PCB Header, with Threaded  
Retention Inserts, Green Housing, 4 Circuits  
**Series Number :** 39526  
**Status :** Active  
**Product Category :** Terminal Blocks and  
Barrier Strip



## Documents & Resources


**Drawings**  
[395265004\\_sd.pdf](#)

**3D Models and Design Files**  
[395265004\\_stp.zip](#)

**Specifications**  
[PS-39500-001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen
- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
  - IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39526
Description	5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 4 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350513135

#### Agency

UL	E48521
----	--------

#### Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

#### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Green
Entry Angle	N/A
Lock to Mating Part	Yes
Net Weight	3.000/g
Number of Rows	1

Orientation	Horizontal
Panel Mount	No
PC Tail Length	3.90mm
PCB Thickness - Recommended	3.20mm
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
5.00mm Pitch Eurostyle Horizontal Plugs	<u>39524</u>
5.00mm Pitch Eurostyle Plugs	<u>39527</u>
Mates With	Most 5.00mm Pitch Industry Standard Plugs

---

This document was generated on Mar 12, 2025