



Color: ■ green

| Technical data     |  |          |
|--------------------|--|----------|
| Number of spacings |  | 3 -times |

| Physical data |  |                        |
|---------------|--|------------------------|
| Depth         |  | 143.6 mm / 5.65 inches |
| Pin spacing   |  | 4.4 mm                 |

| Mechanical data |  |                                  |
|-----------------|--|----------------------------------|
| Suitable        |  | for WAGO WINSTA® MINI Connectors |

| Material data |  |       |
|---------------|--|-------|
| Color         |  | green |
| Fire load     |  | 0 MJ  |
| Weight        |  | 15 g  |

| Commercial data       |  |               |
|-----------------------|--|---------------|
| Product Group         |  | 20 (Winsta)   |
| eCl@ss 10.0           |  | 27-44-06-92   |
| eCl@ss 9.0            |  | 27-44-06-92   |
| ETIM 8.0              |  | EC002863      |
| ETIM 7.0              |  | EC002863      |
| PU (SPU)              |  | 1 pcs         |
| Packaging type        |  | unpacked      |
| Country of origin     |  | DE            |
| GTIN                  |  | 4055143838870 |
| Customs tariff number |  | 82055980000   |



| Environmental Product Compliance |                        |
|----------------------------------|------------------------|
| RoHS Compliance Status           | Compliant,No Exemption |

Downloads

Environmental Product Compliance

| Compliance Search                        |                                                                                   |
|------------------------------------------|-----------------------------------------------------------------------------------|
| Environmental Product Compliance 890-383 |  |

Documentation

| Bid Text |            |                 |                                                                                   |
|----------|------------|-----------------|-----------------------------------------------------------------------------------|
| 890-383  | 19.02.2019 | xml<br>2.59 KB  |  |
| 890-383  | 14.01.2015 | doc<br>22.50 KB |  |

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](https://www.wago.com)