

## Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [M Series](#) >
- [Accessory](#)
- [M5](#)
- [Guided M8](#)
- [M8](#)
- [M10.5](#)
- [M12 \(A\)](#)
- [M12 \(B\)](#)
- [M12 \(D\)](#)
- [M12 \(I\)](#)
- [M12 \(K\)](#)
- [M12 \(L\)](#)
- [M12 \(S\)](#)
- [M12 \(T\)](#)
- [M12 \(X\)](#)
- [M23](#)
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >



### MSXS-08BMMM-PL8X01

Operating Temperature: -40°C ~ +80°C  
Transmission Speed: Cat 6A  
Shielded: Metal, Shielded  
Jacket Material: TPU  
Certificate: N/A

You must login first for view the price


Quantity - 1 +

[Add to Cart](#) [Inquiry](#) 

Can't find? [Customize your part](#)

## Mating Pair & Accessories


Search



M Series, CAP-WBDM SMA2  
-40°C ~ +105°C

- 0 +


☐



M Series, M12, X, M12X-08PFFT  
-55°C ~ +125°C

- 0 +


☐



M Series, M12, X, MSXS-08PFFP  
-40°C ~ +105°C

- 0 +


☐



M Series, M12, X, MSXS-08PFFP  
-40°C ~ +105°C

- 0 +


☐



M Series, M12, X, MSXS-08PFFP  
-40°C ~ +105°C

- 0 +

☐



M Series, M12, X, MSXS-08PFFR  
-40°C ~ +105°C

- 0 +

☐

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current <b>0.5A</b>	Connector Type <b>Overmolded</b>
Shielded <b>Metal, Shielded</b>	No. of Contacts <b>08</b>
Connector Gender <b>Male</b>	Backshell <b>Straight</b>
Mating Style <b>Push Pull</b>	IP Rating <b>IP68</b>
Assembly Style <b>N/A</b>	
<a href="#">More Options</a>	

## People Also Bought

- 

MSXS-08BMMM-...
- 

DC-02BMFB-QL8MPP
- 

ABD-04AFMM-...
- 

CB-03RFMS-RS8DA0
- 

ADD-18BMFC-LL7AP0