

BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip



1400078

<https://www.phoenixcontact.com/us/products/1400078>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, for terminal block width: 5 mm, lettering field size: 4 x 4 mm, Number of individual labels: 10

Commercial data

Item number	1400078
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2112
Catalog page	Page 455 (CL-2007)
GTIN	4017918020118
Weight per piece (including packing)	0.46 g
Weight per piece (excluding packing)	0.46 g
Customs tariff number	39269097
Country of origin	DE

BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip



1400078

<https://www.phoenixcontact.com/us/products/1400078>

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Terminal marking
Pitch	5 mm
Type	high

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Identification technology	Plotter

Dimensions

Width	4 mm
Text field width	4.00 mm
Text field height	4.00 mm
Pitch	5 mm

Material specifications

Color	white
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip



1400078

<https://www.phoenixcontact.com/us/products/1400078>

Mounting type	plug in
---------------	---------

1400078

<https://www.phoenixcontact.com/us/products/1400078>

Classifications

ECLASS

ECLASS-11.0	27281101
ECLASS-12.0	27281101
ECLASS-13.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip



1400078

<https://www.phoenixcontact.com/us/products/1400078>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip



1400078

<https://www.phoenixcontact.com/us/products/1400078>


Accessories

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/us/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver



BN-ZB 5/WH:UNBEDRUCKT - Marker pin Zack strip

1400078

<https://www.phoenixcontact.com/us/products/1400078>



CMS-P1-M/BN-ZB - Magazine insert

5144725

<https://www.phoenixcontact.com/us/products/5144725>

Plastic magazine for CMS-P1 plotter. Accepts 30 marker pins ZB strips



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com