



**Part Number :** 1301040048  
**Product Description :** Haztex Incandescent  
Hazardous and Wet Location Hand Lamp,  
100W, 14/3 SOOW Cord Type, 30.48m (100.0')  
Cord Length  
**Series Number :** 130104  
**Status :** Active  
**Product Category :** Lamps and Lights  
**Engineering Number :** 61430D143



## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Lamps and Lights

Series	130104
Description	Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 14/3 SOOW Cord Type, 30.48m (100.0') Cord Length
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Haztex
Type	Hand Lamps, Specialty Light
UPC	78678861435

## Agency

CSA	LR39801
UL	E30252

## Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Incandescent
Cord Length - Primary	30.48m (100.0')
Cord Length - Secondary	N/A
Cord Type - Primary	14/3 SOOW
Depth	127.00mm (5.000")
Duty	Hazardous, Wet Location
Guard Included	Yes
Guard Type	Cast Aluminum
Height	419.10mm (16.500")
Lamp Type	A21
Length	N/A

Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

---

This document was generated on Jan 11, 2025