Your Expert Partner for **Human Machine Interfaces**

# Actuator

61-
0000.02



https://www.eao.com/component/61-0000.02/en/a...

Downloaded from Arrow.com.

Your product:



# 61-0000.02
# Actuator

## MOUNTING

| | |
|---|---|
| **Mounting type:** | Panel mounting |

## MECHANICAL CHARACTERISTICS

| | |
|---|---|
| **Terminal:** | Plug-in terminal, 2.8 x 0.5 mm |
| **Tightening torque:** | Max. 0.5 Nm |
| **Weight:** | 0.006 kg |

## AMBIENT CONDITION

| | |
|---|---|
| **IP Protection:** | IP40 rear side, according to EN IEC 60529, IP67 front side, according to EN IEC 60529 |
| **Operating temperature:** | – 25 °C ... + 55 °C |
| **Storage temperature:** | – 40 °C ... + 85 °C |


## CERTIFICATE

| | |
|---|---|
| **REACH:** | REACH compliant |
| **RoHS:** | RoHS compliant |

## OTHER


| | |
|---|---|
| **Short Description:** | Actuator, Plug-in terminal, 2.8 x 0.5 mm |
| **Housing material:** | Plastic, according to UL 94 V0, self-extinguishing |
| **Wiring diagrams:** | |


Downloaded from Arrow.com.





**Mounting cut-outs:**

Downloaded from Arrow.com.









**Dimension drawings:**

Downloaded from Arrow.com.




Downloaded from Arrow.com.