



Catalog No. TYB24M

Description: CABLE TIE 30LB 5.5IN NAT NYL WKBOX

UPC No 5414363067054

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 139.7mm (5.5 Inches), Width of 3.56mm (0.14 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Workbench Box Packaging

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 180 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.14 in , 3.56 mm
Length	5.5 in , 139.7 mm
Thickness	0.05 in , 1.31 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000046 Cable tie
Band width	3.56 mm
Length belt/tape/tie	139.7 mm
Length belt/tape/tie	5.5 inch

by ABB

ETIM	EC000046 Cable tie
Tie thickness	1.31 mm
Tie thickness	0.05 inch
Max. bundle diameter	59 mm
Min. holding force	180 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y