Specifications

Photo is representative

Eaton BK/S501-V-63R81

Eaton S501 Series Fast-acting fuse 0.063A, 250 Vac or less, 32 Vdc (self certified), BK-S501-V-63R81

General specifications	
PRODUCT NAME	Eaton Bussmann series S501 fast-acting fuse
CATALOG NUMBER	BK/S501-V-63R81
UPC	051712104555
PRODUCT HEIGHT	97.3 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	1.45 g
WARRANTY	Not Applicable
COMPLIANCES	CCC Marked RoHS Compliant CE Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	BK/S501-V-63R81
PRODUCT TYPE	Fast-acting fuse

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

USED WITH	Axial leads
AMPERAGE RATING	0.063A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	1.5 kAIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Silver-plated endcap construction Ceramic tube
QUANTITY	100
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS	Eaton S501 ceramic tube fuses data sheet Eaton Specification Sheet - BK/S501-V-63R81

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.