

Product data sheet

Specifications

NetBotz Rack Monitor 200 (with 120/240V Power Supply)



NBRK0201

ⓘ Discontinued

Overview

Presentation	Supports up to 12 external sensor pods and up to 78 Universal Sensors.
Lead time	Usually in Stock

Main

Number of rack unit	1U
Number of cables	1
Communication port protocol	HTTP HTTPS SCP SMTP SNMP v1 SNMP v3 SSH v1 SSH v2 TCP/IP Telnet
Provided equipment	Country-specific detachable power cord Documentation CD Installation guide Null-modem cable Rack mounting brackets Temperature/humidity sensor

General

Number of sensor pods supported	12
Number of universal sensors supported	78

Physical

Height	4.3 cm
Width	43.2 cm
Depth	4.3 cm
Product weight	1.43 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Conformance

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	FCC part 15 class A ICES-003
Product certifications	AS/NZS 3548 (C-Tick) class A cUL listed CE low voltage directive 2006/95/EC PSE UL listed VCCI class A VDE

Environmental

Ambient air temperature for operation	0...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C
Storage altitude	0.0000000000...15240.0000000000 m
Storage Relative Humidity	0...95 %

Communications & Management

Communication network type	RJ45 10/100 Base-T
----------------------------	--------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------