

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0537170619
Status: Contact Molex
Description: 2.00mm (.078") Pitch Floating Connector Plug Housing Ass'y, 6 Circuits

Documents:	
3D Model	Product Specification PS-52968-007 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Accessories
Series	53717
Component Type	Adapter
Product Name	N/A
Physical	
Circuits (Loaded)	6
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Number of Rows	2
Packaging Type	Tray
Plating min - Mating	0.254µm (10µ")
Plating min - Termination	2.032µm (80µ")
Polarized to Mating Part	Yes
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-52968-007, RPS-52968-013
Sales Drawing	SD-53717-007

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
53717Series

Use With
52484 , 50837

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION