






PRODUCT NUMBER SEE SHEET 2



spec ref *				dr Rainbow Zhan 2015/08/30		projection 	MM 	size A3	scale 3:2
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Rainbow Zhan 2015/10/23				ecn no -	
				chr Fancy Zhang 2015/10/22					
				appr Pei-Ming Zheng 2015/10/23				product family PwrBlade+	
surface ✓ ASME Y14.5	linear	0.X	±0.5		title 4HDP RA STB HEADER	dwg no 10106132-4000001	rev A		
		0.XX	±0.25						
		0.XXX	±0.10						
	angular	0°	±2°	www.fci.com	cat. no.	Product - Customer Drw		sheet 1 of 3	

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



Copyright FCI.

dr	Rainbow Zhan	2015/08/30	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2
eng	Rainbow Zhan	2015/10/23			ecn no	-		
chr	Fancy Zhang	2015/10/22			rel level	Released		
appr	Pei-Ming Zheng	2015/10/23	product family		PwrBlade+			
	title 4HDP RA STB HEADER				dwg no 10106132-4000001	rev A		
www.fci.com	cat. no.		Product - Customer Drw			sheet 3 of 3		