

Loading...

3ft Cat6a Snagless Shielded (STP) Ethernet Network Patch Cable - Blue

Protect 10 Gigabit data transmissions from 10GBase-T ports and equipment in high noise environments.

★★★★★

5.0

2 Reviews

Roll over image to zoom in

Product # : 00674

Connector 1 : (1) RJ-45 Male

Connector 2 : (1) RJ-45 Male

414 In Stock & ready to ship! ⓘ

1

Add

VISA

MasterCard

AMERICAN EXPRESS

discover

PayPal

pay

Need it shipped today?

Place your order before the timer runs out!

09: 46: 13

print

share

chat

- Product Info
- ★ Customer Reviews
- Questions & Answers
- 🌐 Distributors
- More Choices

- Description
- Certifications
- Specs
- Support

Product Description

This Snagless Shielded Cat6a patch cable is ideal for use with 10GBase-T ports and equipment, such as network adapters, hubs, switches, routers, DSL/cable modems and patch panels, and will protect a high speed 10 Gigabit network connection from noise and electromagnetic interference. For voice/data/video distribution, this cable will handle bandwidth-intensive applications and drastically reduces both impedance and structural return loss (SRL). Each patch cable is fully tested to meet ANSI/TIA 568 C.2 Cat6a component requirements.

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality cable and plugs, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code a network installation. Individual length label on each cable for ease of use.

 **WARNING:** Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Certifications



Product Specifications

Color :	Blue
---------	------

Length :	3.00 Foot
----------	-----------

Jacket Rating :	Standard Non-Rated
UPC :	757120006749
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.122 LB

•Download the technical specifications on this product from the Support tab

Physical Characteristics

- Cable type: Stranded SSTP
- Wiring scheme: 568B
- Temperature rating: 75°C
- Testing: ANSI/TIA 568 C.2 Cat6a component tested

Conductor (4 pair)

- Conductor type: 26AWG (7/0.16) (bare copper)
- Insulation: FM-PE

Overall cable

- Foil shield: Aluminum foil (100% coverage)
- Braided shield: Copper braid (40% coverage)
- Jacket: PVC

Connector

- Connector Type: RJ-45 Male
- Shell: Nickel plated for shielding
- Housing: Polycarbonate,
- Contacts: 50µm gold plated
- Hood: Molded Snagless PVC
- Dimension (L x W x H): 38.2 x 11.6 x 15.1

Product Support

Downloads

- Download the [technical specifications](#)

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**

