





REV.	DATE	DESCRIPTION
NC	05/11/99	INITIAL RELEASE
A	12/18/06	UPDATE DRAWING FORMAT

1/4-36UNS-2B



RECOMMENDED
CABLE STRIPPING DIM'S

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	12/18/06										
6						CHECKED												
5										PART DESCRIPTION SMA DIRECT SOLDER PLUG (FOR .141” SEMI–RIGID, SHORT PROFILE CABLE)								
4						ISSUED												
3	RETAINER RING	BER. COPPER	NATURAL	1		SHEET	1 OF 1											
2	GASKET	SILICONE	RED	1						PART NO. 132266								
1	BODY	BRASS	NICKEL	1														
	DESCRIPTION	MATERIAL	FINISH	QTY				CAD FILE C:/132/132266.DWG		DWG. NO.	132266.DWG		REV.	A	SIZE	A	SCALE	NA