
Part Number : 1300830249
Product Description : Woodhead POW-R-MITE Industrial Duty Cable Reel, 14/3 SOW, 15.24m (50.0') Cord Length
Series Number : 130083
Status : Active
Product Category : Electrical Reels
Engineering Part Number : 9358



Documents and Resources

Drawings

1300830249_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Electrical Reels
Series	130083
Description	Woodhead POW-R-MITE Industrial Duty Cable Reel, 14/3 SOW, 15.24m (50.0') Cord Length
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678879358

Agency

CSA	LR29921
UL	E22769

Electrical

Current - Maximum per Contact	13.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock

Downloaded from Arrow.com.

Cord Length	15.24m (50.0')
Cord Type	14/3 SOW
Depth	0.34m (13.50")
Drum Lock	Ratchet
Duty	Industrial
Guide Arm	5° increments over 270° Arc
Height	0.37m (14.50")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Net Weight	22679.600/g
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	244.35mm (9.620")
Wire Size (AWG)	14

Downloaded from Arrow.com.