

4-Port USB-C Hub, USB 3.x (5Gbps), 4x USB-A Ports, Black

MODEL NUMBER: **U460-004-4AB**



USB 3.1 Type-C hub adds 4 USB-A ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port This USB-C hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive, external hard drive, digital camera, MP3 player and other USB peripherals.

Connects Up to 4 USB-A Peripherals Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and all four provide up to 1.5A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go) **Built-In USB-C Cable Connects in Either Direction**

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The lightweight case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U460-004-4AB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

Specifications

OVERVIEW	
UPC Code	037332209580

Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB ports provide up to 5V/1.5A (7.5W) for charging smartphones and other devices
- Easy installation with plug-and-play operation—no software required

Applications

- Transfer files to and from a USB thumb drive or external hard drive
- Connect your smartphone or other mobile device to build up a full charge
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port.

Package Includes

U460-004-4AB 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt - Black

Product Type	Hub
Technology	USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.656
Built-In Cable Length (m)	0.2
Built-In Cable Length (in.)	7.87
Built-In Cable Length (cm)	20
Bus Powered	Yes
Product Length (in.)	11.7
Product Length (cm.)	29.72
Product Length (ft.)	0.98
Product Length (m)	0.3
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	0.7
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Connection to Power)
CHARGING	
Total Charging Watts	7.5
Charging Ports	USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(4) 1.5A

PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	1.06 x 3.00 x 5.70
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.840 x 3.800 x 1.200
Unit Dimensions (hwd / cm)	2.14 x 9.65 x 3.05
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No



1000 Eaton Boulevard
Cleveland, OH 44122
United States

STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.