



Sensing and Control

Honeywell.com Test & Measurement

Search the entire website and product database

Start Here ...

Search

HOME

ABOUT US

KEY INDUSTRIES SERVED

PRODUCTS & INFORMATION

NEWS & EVENTS

SALES & SUPPORT

LOGIN

LSXYAB3K([Home](#) : [Products](#) : [basics](#) : [Switches](#) : [MICRO SWITCH™ Hazardous Location Switches](#) : [LSX](#))

Explosion-Proof Limit Switches LSX Non Plug-in: Low Temperature Version;
Side Rotary; 1NC 1NO SPDT Snap Action; 0.5 in - 14NPT conduit

Lever NOT included

Actual product
appearance may vary.

Sales & Service

Distributor Inventory

Distributor Inventory

Input part number for stock availability

Narrow Your Search**Modify Your Search****Products****Technology****Industries Served**

Overview

Specs

Documentation

Application Notes

Product Specifications

Availability	Global
Operating Force (OF)	0.45 Nm [4 in lb] max.
Pretravel (PT)	15° max.
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Weather-Sealed, Explosion-Proof Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double-Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	LSX Non Plug-in
Series Name	LSX
Sealing	NEMA 1, 3, 4, 6, 7 (Class 1, Division 1, Groups B, C, D), 9 (Class 2, Division 1, Groups E, F, G), 13
CSA File #	LR57327
UL File #	E61730
Operating Temperature	-40 °C to 121 °C [-40 °F to 250 °F]
Comment	Low Temperature Construction
Agency Approvals and Standards	UL, CSA
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Explosion-proof

Product Search

Product Type:	All Product Types
Industry:	All Industries
Search Term:	Start Here ...

New Products Only
 Entire Product Catalog

Search

My Links

eCOM Login
Request Access to eCOM
Rep/AD Portal Login
Rep/AD Portal Access Request
Sample Request
Digital University Login
Limitless Microsite
Supplier Microsite

Literature and Media

Application Demos
White Papers
Application Notes
Literature Request
Data Sheets
Videos

Contacts

Customer Service
Technical Support
Global Sales & Service
Website Feedback



[Terms & Conditions](#)

[Privacy Statement](#)

[Site Map](#)