



Catalog No. TYH24M

Description: CABLE TIE 40LB 5IN GR NYL HEAT STBL

UPC No 786210810966

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint for Temperatures up to 105 Degrees Celsius (221 F) for Indoor Applications, Length of 138mm (5.4 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 35mm (1.38 Inch), Tensile Strength Rating of 180 Newtons (40 Pounds)

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Green
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds , 180 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.14 in , 3.56 mm
Length	5.4 in , 138 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	Max 1.38 in , Max 35 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	138 mm
Length belt/tape/tie	5.43 inch

by ABB

ETIM	EC000046 Cable tie
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	35 mm
Min. holding force	180 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Surface protection	Untreated
Halogen free	Y
Colour	Green
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	1349334_2014-11-06	N/A
UL	E49405	N/A	ZODZ	N/A	N/A