

PRODUCT-DETAILS

HSB250

SHRINK KON BOX - 7,5M BLACK



General Information

Extended Product Type	HSB250
Product ID	7TCA017300R0334
EAN	5414363076896
Catalog Description	SHRINK KON BOX - 7,5M BLACK
Long Description	Thin Wall Heat Shrink Tubing in Dispenser Box - 1/4 Inch Expanded Inside Diameter - 7.5 Meters, Black, Shrink Ratio 2:1, CrossLinked Polyolefin, Item is Silicone, Cadmium and Lead Free

Ordering

EAN	5414363076896
UPC	786210526799
Country of Origin	Germany (DE)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Depth /	24.6 in
Length	7.5 m

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	2.4 in 61 mm
Package Level 1 Height	6.7 in 170 mm
Package Level 1 Depth / Length	6.7 in 170 mm
Package Level 2 Units	60 piece
Package Level 2 Width	15.8 in 401 mm
Package Level 2 Height	22.5 in 572 mm
Package Level 2 Depth / Length	20.9 in 531 mm

Additional Information

Brand / Label	Shrink-Kon
Color	Black
Dielectric Test Voltage	280/Mil (11kV/mm) V
Effective Date	19980621
Flammability Hazard Rating	Self Extinguishing
Process Temperature Rating	-67 to +212 °F -55 to +100 °C
Product Name	PLASTIC CONDUIT
Product Type	Thin-Wall Heat Shrinkable Tubing
RoHS Date	9AKK107992A8965
Shrink Ratio	2:1
Shrink Temperature	230 °F 110 °C
Thickness	Thin
Water Absorption	0.03%

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	HSB250
Instructions and Manuals	HSB250
REACH Declaration	9AKK108466A3888
RoHS Information	9AKK107992A8965

Classifications

ETIM 6	EC000217 - Shrink tubing
ETIM 7	EC000217 - Shrink tubing
ETIM 8	EC000217 - Shrink tubing
UNSPSC	39121723
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5073 >> Heat shrinkable tube

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Identification & Heat Shrink

